

# Eaton TR7766B-BOX

Catalog Number: TR7766B-BOX

Eaton combination 3.6A USB charger with duplex receptacle, 20A, 125V, B - TR7766B-BOX



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton combination USB charger with duplex receptacle	TR7766B-BOX
	<b>UPC</b>
	032664767036
<b>Product Length/Depth</b>	<b>Product Height</b>
1.4 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
1.3 in	0.793 lb
<b>Certifications</b>	
cULus Listed	

## defaultTaxonomyAttributeLabel

### Type

Type A

### Amperage Rating

20A

### Voltage rating

125 V

### Contact material

Brass

### Features

Tamper resistant

3.6A Charging

### Wiring method

Screw terminals

### Number of wires

Three-wire

### Mounting method

Flush

### Number Of Poles

Two-pole

### Packaging type

Retail Box

### Color

Brown

### Material

Thermoplastic

### Style

Decorator

### Allowable wire size

#12-14 AWG

### NEMA configuration

5-20R

### Torque rating

14 lbf-inch

### Combination type

USB

## Resources

### Brochures

[USB Duplex Receptacle Devices Brochure](#)

### Multimedia

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

[Eaton's USB charging receptacles - Never miss a moment](#)

[Introduction to USB-C Duplex Receptacles](#)

### Specifications and datasheets

[Combination USB 3.6A charger with TR duplex receptacle](#)

[Eaton Specification Sheet - TR7766B-BOX](#)

Design type

Receptacle

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)