

Eaton TRUSBC20W-BOX

Catalog Number: TRUSBC20W-BOX

Eaton Combination USB Type-C Charger, 20A 5-20R Receptacle, 5A, 125 Vac, White, Box



General specifications

Product Name	Catalog Number
Eaton combination USB charger with duplex receptacle	TRUSBC20W-BOX
	UPC
	032664753428
Product Length/Depth	Product Height
1.4 in	4.19 in
Product Width	Product Weight
1.3 in	0.285 lb
Certifications	
NOM	
cULus Listed	

defaultTaxonomyAttributeLabel

Type

Type C

Amperage Rating

20A

Voltage rating

125 V

Contact material

Brass

Features

Tamper resistant

5A Charging

Wiring method

Screw terminals

Number of wires

3

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Packaging type

Retail Box

Color

White

Brown

Material

Thermoplastic

Style

Decorator

Allowable wire size

#12-14 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Combination type

Resources

Brochures

[5A Slim USB Charging Receptacles](#)

[USB charging devices brochure](#)

Multimedia

[Introduction to USB-C Duplex Receptacles](#)

[Eaton's USB charging receptacles - Never miss a moment](#)

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TRUSBC20W-BOX](#)

[Combination USB-C charger with TR duplex receptacle spec sheet](#)

USB

Design type

Receptacle

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)