

# Eaton 7511V-BOX

Catalog Number: 7511V-BOX

Eaton standard grade decorator switch, Lighted in off position, box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Maintained, Ivory, Motor Control, Fan, LED, Incand, Florscnt, Halogen, Single-pole, Thermoplastic 627996



## General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7511V-BOX
UPC	Product Length/Depth
032664627996	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.001 lb	NAFTA
	RoHS Compliant
Certifications	
cULus Listed	

## defaultTaxonomyAttributeLabel

### Allowable wire size

#14-12 AWG

### Special features

Lighted in off position, box

### Type

Switch decorator

### Amperage Rating

15A

### Voltage rating

120/277 V

### Number Of Poles

Single-pole

### Phase

Single-phase

### Wiring method

Back and push

### Switch type

Single-pole

### Mounting method

Flush

### Closure type

Maintained

### Load type

HAL

ELV

MLV

FLR

INC

Motor Control

CFL

LED

Fan

### Material

Thermoplastic

### Actuator

Decorator

## Resources

### Catalogs

[Residential Buyers Guide B-04](#)

### Specifications and datasheets

[Eaton Specification Sheet - 7511V-BOX](#)

Color

Ivory

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)