

Eaton AH18203I-C

Catalog Number: AH18203I-C

Eaton Arrow Hart industrial grade toggle switch, 15A, Flush, 347V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Three-Way

General specifications

Product Name	Catalog Number
Eaton Arrow Hart industrial grade toggle switch	AH18203I-C
	UPC
	040893657363
Product Length/Depth	Product Height
1.36 in	3.28 in
Product Width	Product Weight
1.05 in	0.22 lb
Certifications	
cUL Listed	



defaultTaxonomyAttributeLabel

Type

Toggle switch

Amperage Rating

15A

Voltage rating

347 V

Number Of Poles

Single-pole

Application

Industrial

Wiring method

Back and side

Switch type

Three-way

Mounting method

Flush

Connector type

Screw

Load type

CFL

FLR

INC

Fan

Motor Control

LED

HAL

MLV

ELV

Material

Polycarbonate

Number of ways

Three-way

Allowable wire size

#14-10 AWG

Torque rating

14 lbf-inch

Color

Resources

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Eaton Specification Sheet - AH182031-C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)