BORESCOPE SELECTION GUIDE

	ET17 Utility Borescope	FI18 Plumber's Borescope	ET19 Pro Borescope (Coming Soon!)
Snake	10ft Nylon	5ft Armored	10ft Armored
Camera Resolution	1280x720p	1280x720p	1280x720p
Number of Lenses	Single	Single	Dual
Camera Head Size	5.5mm	5.5mm	5.5mm
Number of LED Lights	6	6	6
Screen Size	4.3"	4.3"	4.3"
Display Resolution	854x480p	854x480p	854x480p
Included Attachments	Hook, Magnet, Mirror	Hook, Magnet, Mirror	Hook, Magnet
IP - Camera Head	IP67	IP67	IP67
Internal Storage	2GB	2GB	2GB
Image/Video Transfer	USB-C	USB-C	USB-C/Wi-Fi
Photo Capture	•	•	•
Video Capture	•	•	•
Digital Zoom	Yes	Yes	Yes
Included	Borescope; 5.5mm Camera with 10' (3m) Snake; USB-C Cable; Camera Accessories: Magnet, Hook, Mirror; Carrying Case	Borescope, 5.5mm Camera with 5' (1.5m) Armored Snake, USB-C Ca- ble, Camera Accessories: Magnet, Hook, Mirror; Carrying Case	Borescope; 5.5mm Camera with 10' (3m) Armored Snake; USB-C Cable; Camera Accessories: Magnet, Hook; Carrying Case
Battery Type	USB-C Rechargeable Lithium-Ion 2000 mAh, 7.4 Wh	USB-C Rechargeable Lithium-Ion 2000 mAh, 7.4 Wh	USB-C Rechargeable Lithium-Ion 2000 mAh, 7.4 Wh
Overall Height	1.51" (3.8 cm)	1.51" (3.8 cm)	1.51" (3.8 cm)
Overall Length	6.55" (16.6 cm)	6.55" (16.6 cm)	6.55" (16.6 cm)
Overall Width	3.19" (8.1 cm)	3.19" (8.1 cm)	3.19" (8.1 cm)
Weight	8.6 oz (244 g)	8.6 oz (244 g)	8.6 oz (244 g)
Certifications	CE and UKCA	CE and UKCA	CE and UKCA

