

Specification Sheet

Part Number: T120R0PPH4



Polypropylene cable ties deliver excellent resistance to chemicals and salts.

Inside serrations provide strong grip on cables and wire bundles.

Easy application either manually or with a tensioning tool.

Bent tail ensures a quick and simple installation.

Cable Tie, 15" Long, 60lb Tensile Strength, PP, Black, 500/pkg

Article Number 111-12066

Type T120R

Color Black (BK)

Quantity Per bag

Product Description
HellermannTyton's polypropylene cable ties offer added resistance to most chemicals. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Cable Tie, 15" Long, 60lb Tensile Strength, PP, Black, 500/pkg

Global Part Name T120R-PP-BK

Minimum Tensile Strength (Imperial) 60.0

Minimum Tensile Strength (Metric) 535

Length L (Imperial) 15.0

Length L (Metric) 387.0

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.30

Width W (Metric) 7.6

Bundle Diameter Min (Imperial) 0.50

Bundle Diameter Min (Metric) 5.0

Bundle Diameter Max (Imperial) 4.13

Bundle Diameter Max (Metric) 105.0

Thickness T (Imperial) 0.07

Thickness T (Metric)	1.8
Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach

to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)