

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Precision-machined tips for exact fit. Handle marked for easy identification of screwdriver size, type and length.. Strong, durable black phosphate tips prevent chipping of plating. Soft, cushioned grip for extra comfort and torque

PRODUCT NAME –

Page Title

Square Shank 5/16" x 6" Flat Blade Screwdriver

PRODUCT OVERVIEW –

Marketing Text 1

Precision-machined tips for exact fit

Marketing Text 2

Handle marked for easy identification of screwdriver size, type and length.

Marketing Text 3

Strong, durable black phosphate tips prevent chipping of plating

Marketing Text 4

Soft, cushioned grip for extra comfort and torque

Marketing Text 5

Exceeds ASME/ANSI specifications

Marketing Text 6

Lifetime limited warranty

Marketing Text 7

Note: This is not an insulated tool

PRODUCT SPECIFICATION –

Product Specification 1

Finish : Black Phosphate Plated Tip

Product Specification 2

Handle Type : Soft, Cushioned Grip

Product Specification 3

Overall Length : 10-15/16 IN (27.800 CM)

Product Specification 4

Shank Length : 6.000 IN

Product Specification 5

Shank Shape : Square

Product Specification 6

Standard : ASME/ANSI

Product Specification 7

Tip Size : 5/16 IN

Product Specification 8

Tip Type : Keystone

Product Specification 9

Type : Heavy Duty, Flat Blade

Product Specification 10

Weight : 0.400 LB (0.180 KG)