

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Narrow cabinet tip for limited access applications. Handle marked for easy identification of screwdriver size, type and length. Precision-machined tips for accurate fastener contact. Strong, durable black phosphate tips prevent chipping of plating

PRODUCT NAME –

Page Title

Round Shank 3/16" X 6" Flat Blade Screwdriver

PRODUCT OVERVIEW –

Marketing Text 1

Narrow cabinet tip for limited access applications

Marketing Text 2

Handle marked for easy identification of screwdriver size, type and length

Marketing Text 3

Precision-machined tips for accurate fastener contact

Marketing Text 4

Strong, durable black phosphate tips prevent chipping of plating

Marketing Text 5

Soft, cushioned grip for extra comfort and torque

Marketing Text 6

Exceeds ASME/ANSI specifications

Marketing Text 7

Lifetime limited warranty

Marketing Text 8

Note: This is not an insulated tool

PRODUCT SPECIFICATION –

Product Specification 1

Finish : Black Phosphate Plated Tip

Product Specification 2

Handle Type : Soft, Cushioned Grip

Product Specification 3

Overall Length : 9-3/4 IN (24.800 CM)

Product Specification 4

Shank Length : 6.000 IN

Product Specification 5

Shank Shape : Round

Product Specification 6

Standard : ASME/ANSI

Product Specification 7

Tip Size : 3/16 IN

Product Specification 8

Tip Type : Cabinet

Product Specification 9

Type : Heavy Duty, Flat Blade

Product Specification 10

Weight : 0.180 LB (0.080 KG)