

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Narrow cabinet tip for limited access applications. Handle marked for easy identification of screwdriver size, type and length. Precision-machined tips for accurate fastener contact. Strong, durable black phosphate tips prevent chipping of plating

**PRODUCT NAME –**

---

**Page Title**

Round Shank 3/16" X 10" Flat Blade Screwdriver

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Narrow cabinet tip for limited access applications

**Marketing Text 2**

Handle marked for easy identification of screwdriver size, type and length

**Marketing Text 3**

Precision-machined tips for accurate fastener contact

**Marketing Text 4**

Strong, durable black phosphate tips prevent chipping of plating

**Marketing Text 5**

Soft, cushioned grip for extra comfort and torque

**Marketing Text 6**

Exceeds ASME/ANSI specifications

**Marketing Text 7**

Lifetime limited warranty

**Marketing Text 8**

Note: This is not an insulated tool

**PRODUCT SPECIFICATION –**

---

**Product Specification 1**

Finish : Black Phosphate Plated Tip

**Product Specification 2**

Handle Type : Soft, Cushioned Grip

**Product Specification 3**

Overall Length : 13-3/4 IN (34.900 CM)

**Product Specification 4**

Shank Length : 10.000 IN

**Product Specification 5**

Shank Shape : Round

**Product Specification 6**

Standard : ASME/ANSI

**Product Specification 7**

Tip Size : 3/16 IN

**Product Specification 8**

Tip Type : Cabinet

**Product Specification 9**

Type : Heavy Duty, Flat Blade

**Product Specification 10**

Weight : 0.220 LB (0.100 KG)