

## 2024 Specification Sheet - English

---



### LONG DESCRIPTION –

---

#### **Long Description Marketing Copy**

Rugged hollow shaft for screw clearance. Heavy-duty construction for longer life. Handle and shaft marked for easy identification of nut driver size. Precision 6-point sockets for accurate fastener fit

### PRODUCT NAME –

---

#### **Page Title**

7-Piece Nut Driver Set (3" Shank): Sizes 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", & 1/2"

### PRODUCT OVERVIEW –

---

#### **Marketing Text 1**

Rugged hollow shaft for screw clearance

#### **Marketing Text 2**

Heavy-duty construction for longer life

#### **Marketing Text 3**

Handle and shaft marked for easy identification of nut driver size

#### **Marketing Text 4**

Precision 6-point sockets for accurate fastener fit

#### **Marketing Text 5**

High-grade, rust resistant, chrome-plated finish

### **Marketing Text 6**

Soft, cushioned grip for extra comfort and torque

### **Marketing Text 7**

Exceeds ASME/ANSI specifications.

### **Marketing Text 8**

Lifetime limited warranty

### **Marketing Text 9**

Note: This is not an insulated tool

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Finish : Chrome Plated

### **Product Specification 2**

Includes : Sizes 3/16 IN, 1/4 IN, 5/16 IN, 11/32 IN, 3/8 IN, 7/16 IN And 1/2 IN

### **Product Specification 3**

Number Of Pieces : 7

### **Product Specification 4**

Shank Length : 3.000 IN

### **Product Specification 5**

Shank Type : Hollow

### **Product Specification 6**

Standard : ASME/ANSI

### **Product Specification 7**

Type : Standard, Heavy Duty

### **Product Specification 8**

Weight : 1.650 LB (0.750 KG)