

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Rugged hollow shaft for bolt clearance. Heavy-duty construction for longer life. Handle color marked for easy identification of nut driver size. Precision 6-point sockets for accurate fastener fit

PRODUCT NAME –

Page Title

Heavy-Duty Nut Driver 3/8" X 3"

PRODUCT OVERVIEW –

Marketing Text 1

Rugged hollow shaft for bolt clearance

Marketing Text 2

Heavy-duty construction for longer life

Marketing Text 3

Handle color marked for easy identification of nut driver size

Marketing Text 4

Precision 6-point sockets for accurate fastener fit

Marketing Text 5

High-grade, rust resistant, chrome-plated finish

Marketing Text 6

Soft, cushioned grip for extra comfort and torque

Marketing Text 7

Exceeds ASME/ANSI specifications

Marketing Text 8

Lifetime limited warranty

Marketing Text 9

Note: This is not an insulated tool

PRODUCT SPECIFICATION –

Product Specification 1

Drive Size : 3/8 IN

Product Specification 2

Finish : Chrome Plated

Product Specification 3

Overall Length : 7-5/16 IN (18.600 CM)

Product Specification 4

Shank Length : 3.000 IN

Product Specification 5

Shank Type : Hollow

Product Specification 6

Standard : ASME/ANSI

Product Specification 7

Type : Standard, Heavy Duty

Product Specification 8

Weight : 0.200 LB (0.090 KG)