

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Precision tip for accurate fastener fit. Handle marked and color coded for easy identification of screwdriver size and type. Heavy-duty construction for longer life. High-grade, rust resistant, chrome-plated finish

PRODUCT NAME –

Page Title

Square-Recess Tip Driver - #2 x 4"

PRODUCT OVERVIEW –

Marketing Text 1

Precision tip for accurate fastener fit

Marketing Text 2

Handle marked and color coded for easy identification of screwdriver size and type

Marketing Text 3

Heavy-duty construction for longer life

Marketing Text 4

High-grade, rust resistant, chrome-plated finish

Marketing Text 5

Soft, cushioned grip for extra comfort and torque

Marketing Text 6

Exceeds ASME/ANSI specifications

Marketing Text 7

Lifetime limited warranty

Marketing Text 8

Note: This is not an insulated tool

PRODUCT SPECIFICATION –

Product Specification 1

Blade Finish : Chrome Plated

Product Specification 2

Handle Type : Soft, Cushioned Grip

Product Specification 3

Overall Length : 8-1/4 IN (21.000 CM)

Product Specification 4

Shank Length : 4.000 IN

Product Specification 5

Standard : ASME/ANSI

Product Specification 6

Tip Size : #2

Product Specification 7

Tip Type : Square Recess

Product Specification 8

Type : Heavy Duty

Product Specification 9

Weight : 0.300 LB (0.140 KG)