

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Precision tip for accurate fastener fit. Handle marked and color coded for easy identification of screwdriver size and type. Heavy-duty construction for longer life. High-grade, rust resistant, chrome-plated finish

**PRODUCT NAME –**

---

**Page Title**

Square-Recess Tip Driver - #2 x 8"

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Precision tip for accurate fastener fit

**Marketing Text 2**

Handle marked and color coded for easy identification of screwdriver size and type

**Marketing Text 3**

Heavy-duty construction for longer life

**Marketing Text 4**

High-grade, rust resistant, chrome-plated finish

**Marketing Text 5**

Soft, cushioned grip for extra comfort and torque

**Marketing Text 6**

Exceeds ASME/ANSI specifications

**Marketing Text 7**

Lifetime limited warranty

**Marketing Text 8**

Note: This is not an insulated tool

**PRODUCT SPECIFICATION –**

---

**Product Specification 1**

Blade Finish : Chrome Plated

**Product Specification 2**

Handle Type : Soft, Cushioned Grip

**Product Specification 3**

Overall Length : 11-3/4 IN (29.800 CM)

**Product Specification 4**

Shank Length : 8.000 IN

**Product Specification 5**

Standard : ASME/ANSI

**Product Specification 6**

Tip Size : #2

**Product Specification 7**

Tip Type : Square Recess

**Product Specification 8**

Type : Heavy Duty

**Product Specification 9**

Weight : 0.400 LB (0.180 KG)