

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Wood-type auger bit with screw point. Pulls itself through wood, avoids walking or skidding. Excellent for drilling in soft woods or through thin sections. Slow back-taper allows for easy retrieval

PRODUCT NAME –

Page Title

.500 X .187 X 54 D'VersiBIT® Bit

PRODUCT OVERVIEW –

Marketing Text 1

Wood-type auger bit with screw point

Marketing Text 2

Pulls itself through wood, avoids walking or skidding

Marketing Text 3

Excellent for drilling in soft woods or through thin sections

Marketing Text 4

Slow back-taper allows for easy retrieval

PRODUCT SPECIFICATION –

Product Specification 1

Application : For Drilling In Soft Woods Or Through Thin Sections

Product Specification 2

Bit Diameter : 1/2 IN (12.700 MM)

Product Specification 3

Color Code : Green

Product Specification 4

Shaft Diameter : 3/16 IN (4.800 MM)

Product Specification 5

Shaft Length : 54.000 IN (1371.600 MM)

Product Specification 6

Sub Brand : D'VersiBIT®

Product Specification 7

Type : Type A