

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Progressive-pitch reciprocating saw blades cut a wide range of standard construction materials quickly and cleanly - regardless of thickness. Bi-metal construction provides maximum flexibility and break resistance - plus lasting sharpness. Exclusive plunge tip makes starting cuts faster and easier. Blades color coded by application

PRODUCT NAME –

Page Title

6" x 24T Reciprocating Saw Blade (Pack of 5)

PRODUCT OVERVIEW –

Marketing Text 1

Progressive-pitch reciprocating saw blades cut a wide range of standard construction materials quickly and cleanly - regardless of thickness

Marketing Text 2

Bi-metal construction provides maximum flexibility and break resistance - plus lasting sharpness

Marketing Text 3

Exclusive plunge tip makes starting cuts faster and easier

Marketing Text 4

Blades color coded by application

PRODUCT SPECIFICATION –

Product Specification 1

Application : For Metal

Product Specification 2

Length : 6.000 IN (152.000 MM)

Product Specification 3

Material : Bi-Metal

Product Specification 4

Package : 5/Pack

Product Specification 5

Teeth Per Inch : 24 TPI

Product Specification 6

Thickness : 0.350 IN (8.890 MM)

Product Specification 7

Type : Reciprocating, Straight

Product Specification 8

Width : 3/4 IN (19.050 MM)