

## 2024 Specification Sheet - English

---



### LONG DESCRIPTION –

---

#### **Long Description Marketing Copy**

Progressive-pitch reciprocating saw blades cut a wide range of standard construction materials quickly and cleanly - regardless of thickness. Bi-metal construction provides maximum flexibility and break resistance - plus lasting sharpness. Exclusive plunge tip makes starting cuts faster and easier. Blades color coded by application

### PRODUCT NAME –

---

#### **Page Title**

8" x 18T Reciprocating Saw Blades

### PRODUCT OVERVIEW –

---

#### **Marketing Text 1**

Progressive-pitch reciprocating saw blades cut a wide range of standard construction materials quickly and cleanly - regardless of thickness

#### **Marketing Text 2**

Bi-metal construction provides maximum flexibility and break resistance - plus lasting sharpness

#### **Marketing Text 3**

Exclusive plunge tip makes starting cuts faster and easier

#### **Marketing Text 4**

Blades color coded by application

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Application : For Metal

### **Product Specification 2**

Length : 8.000 IN (203.000 MM)

### **Product Specification 3**

Material : Bi-Metal

### **Product Specification 4**

Package : 5/Pack

### **Product Specification 5**

Teeth Per Inch : 18 TPI

### **Product Specification 6**

Thickness : 0.500 IN (12.700 MM)

### **Product Specification 7**

Type : Reciprocating, Straight

### **Product Specification 8**

Width : 3/4 IN (19.050 MM)