

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

34 - 10 AWG (0.08 - 6 MM²) stripping capacity. 12 AWG (4 MM²) solid, 10 AWG (6 MM²) stranded capacity. Strips and cuts flat and round cable. Self-adjusts to different wire gauges

PRODUCT NAME –

Page Title

Kwik Stripper® Wire Stripper

PRODUCT OVERVIEW –

Marketing Text 1

34 - 10 AWG (0.08 - 6 MM²) stripping capacity

Marketing Text 2

12 AWG (4 MM²) solid, 10 AWG (6 MM²) stranded capacity

Marketing Text 3

Strips and cuts flat and round cable

Marketing Text 4

Self-adjusts to different wire gauges

Marketing Text 5

Laminated steel blades minimize the risk of nicking conductors

Marketing Text 6

Front entry jaws have an adjustable strip length guide

Marketing Text 7

Lightweight reinforced nylon is chemical and corrosion resistant

Marketing Text 8

Note: This is not an insulated tool

PRODUCT SPECIFICATION –

Product Specification 1

Application : Strips And Cuts Flat And Round Cable

Product Specification 2

Capacity : 34-10 AWG (0.080 - 6.000 MM²), 12 AWG (4 MM²) Solid, 10 AWG(6 MM²) Stranded

Product Specification 3

Handle Type : Lightweight Reinforced Nylon

Product Specification 4

Material : Steel Blade

Product Specification 5

Replacement Part : 20243 Blade Cassette

Product Specification 6

Sub Brand : Kwik Stripper