

## 2024 Specification Sheet - English

---



### LONG DESCRIPTION –

---

#### **Long Description Marketing Copy**

Double-braided inner core with an extra double-braided outer jacket for added strength and less stretch. White with green tracer. Rot and mildew resistant. Factory spliced eyes at both ends

### PRODUCT NAME –

---

#### **Page Title**

1/2" X 600' Double-Braided Composite Rope

### PRODUCT OVERVIEW –

---

#### **Marketing Text 1**

Double-braided inner core with an extra double-braided outer jacket for added strength and less stretch

#### **Marketing Text 2**

White with green tracer

#### **Marketing Text 3**

Rot and mildew resistant

#### **Marketing Text 4**

Factory spliced eyes at both ends

#### **Marketing Text 5**

Select a rope with a maximum rated capacity that meets or exceeds the cable puller's maximum pulling force

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Package Configuration : Wooden Spool

### **Product Specification 2**

Breaking Strength : 10000.000 LB (44.400 KN) Average

### **Product Specification 3**

Color : White With Green Tracer

### **Product Specification 4**

Rope Diameter : 1/2"

### **Product Specification 5**

Working Load Limit : Breaking Strength : 10000.000 LB (44.400 KN) Average

### **Product Specification 6**

Rope Type : Composite, Double Braided

### **Product Specification 7**

Standard : Double-Braided Composite Rope for Cable Pullers

### **Product Specification 8**

Type : Rope

### **Product Specification 9**

Application : Electrical Cable pull

### **Product Specification 10**

Maximum Rated Capacity : 2200 LB (8.900 KN)

### **Product Specification 11**

Rope Length : 600.000 FT (182.000 M)

### **Product Specification 12**

Rope Stand : 644