

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Fish sticks kit comes with highly visible green color rods that can be easily threaded together and seen when working above ceilings, down walls, or under raised floors. 1/4 IN (6.4 mm) diameter fiberglass adds rigidity when connecting multiple sections. 200 lbs. (0.9 kN) maximum pulling strength. Two different threaded tips accommodate various bundles of wire or cable

**PRODUCT NAME –**

---

**Page Title**

Short Fishstix Kit

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Fish sticks kit comes with highly visible green color rods that can be easily threaded together and seen when working above ceilings, down walls, or under raised floors

**Marketing Text 2**

1/4 IN (6.4 mm) diameter fiberglass adds rigidity when connecting multiple sections

**Marketing Text 3**

200 lbs. (0.9 kN) maximum pulling strength

**Marketing Text 4**

Two different threaded tips accommodate various bundles of wire or cable

### **Marketing Text 5**

540-24 includes one 3 IN (0.9 mm) Glo Stix section for improved tip visibility

### **Marketing Text 6**

Optional Whisk Nose Tip is available for fishing over obstacles, and can be used to guide extended Glo Stix sideways above ceilings by rotating. Can also be used to fish longer lengths by providing a tip that can be snagged from the opposite direction with another extended Fish or Glo Stix with a hook nose tip

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Sub Brand : Fish Stix

### **Product Specification 2**

Size : 1/4" x 12' (6.4 mm x 3.6 m)

### **Product Specification 3**

Tensile Strength : 200.000 LB (0.900 KN) Maximum Pulling Strength

### **Product Specification 4**

Color : Green

### **Product Specification 5**

Diameter : 1/4 IN (6.400 MM)

### **Product Specification 6**

Includes : Bullet And "J" Hook Nose Tips

### **Product Specification 7**

Accessory : 10497 Hook Nose Tip, 10498 Bullet Nose Tip, 11426 Whisk Nose Tip

### **Product Specification 8**

Replacement Part : 11583G 1/4 IN X 4 FT Fish Stix Section, 11584 1/4 IN X 6 FT Fish Stix Section, 12920 3/16 IN X 20 IN Glo Stix Section, 11585 3/16 IN x 3 FT Glo Stix Section, 11427 3/16 IN x 5 FT Glo Stix Section, 12922G 5/32 IN X 4 FT Glo Stix Section, 89803 5/32 IN X 6 FT

### **Product Specification 9**

Minimum Bend Radius : 6-1/2 IN (165.000 MM)

### **Product Specification 10**

Section Length : 4.000 FT (1.200 M)

### **Product Specification 11**

Sections : 3