

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Luminescent fiberglass rods glow in the dark to make fishing voice, data and video wires easier in dark spaces, such as above ceilings, in walls, and below sub-floors. More flexible for fishing in walls through outlet box holes. Sturdy, steel-threaded connectors are interchangeable with Greenlee Tools' 1/4 IN (6.4 mm) Fish Stix. Clear, non-metallic storage tube keeps Glo Stix charged and ready to use

PRODUCT NAME –

Page Title

Glo Stix Kit

PRODUCT OVERVIEW –

Marketing Text 1

Luminescent fiberglass rods glow in the dark to make fishing voice, data and video wires easier in dark spaces, such as above ceilings, in walls, and below sub-floors

Marketing Text 2

More flexible for fishing in walls through outlet box holes

Marketing Text 3

Sturdy, steel-threaded connectors are interchangeable with Greenlee Tools' 1/4 IN (6.4 mm) Fish Stix

Marketing Text 4

Clear, non-metallic storage tube keeps Glo Stix charged and ready to use

Marketing Text 5

200 lbs.. (0.9 kN) maximum pulling strength

Marketing Text 6

Optional Whisk Nose Tip is available for fishing over obstacles, and can be used to guide extended Glo Stix sideways above ceilings by rotating

Marketing Text 7

Can also be used to fish longer lengths by providing a tip that can be snagged from the opposite direction with another extended Fish or Glo Stix with a hook nose tip

PRODUCT SPECIFICATION –

Product Specification 1

Sub Brand : Glo Stix

Product Specification 2

Size : 3/16" X 15' (4.7 mm X 4.6 m)

Product Specification 3

Tensile Strength : 200.000 LB (0.900 KN) Maximum Pulling Strength

Product Specification 4

Diameter : 3/16 IN (4.700 MM)

Product Specification 5

Includes : Bullet And "J" Hook Nose Tips

Product Specification 6

Accessory : 10497 Hook Nose Tip, 10498 Bullet Nose Tip, 11426 Whisk Nose Tip

Product Specification 7

Replacement Part : 11583G 1/4 IN X 4 FT Fish Stix Section, 11584 1/4 IN X 6 FT Fish Stix Section, 12920 3/16 IN X 20 IN Glo Stix Section, 11585 3/16 IN x 3 FT Glo Stix Section, 11427 3/16 IN x 5 FT Glo Stix Section, 12922G 5/32 IN X 4 FT Glo Stix Section, 89803 5/32 IN X 6 FT

Product Specification 8

Minimum Bend Radius : 4-1/4 IN (108.000 MM)

Product Specification 9

Section Length : 5.000 FT (1.500 M)

Product Specification 10

Sections : 3