

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Highly visible green color rods can be easily threaded together and seen when working above ceilings, down walls, or under raised floors. 1/4 IN (6.4 mm) diameter fiberglass adds rigidity when connecting multiple sections. 200 lbs (0.9 kN) maximum pulling strength. Two different threaded tips accommodate various bundles of wire or cable

PRODUCT NAME –

Page Title

Fish Stix™ Kit: 1/4" X 24'

PRODUCT OVERVIEW –

Marketing Text 1

Highly visible green color rods can be easily threaded together and seen when working above ceilings, down walls, or under raised floors

Marketing Text 2

1/4 IN (6.4 mm) diameter fiberglass adds rigidity when connecting multiple sections

Marketing Text 3

200 lbs (0.9 kN) maximum pulling strength

Marketing Text 4

Two different threaded tips accommodate various bundles of wire or cable

Marketing Text 5

540-24 includes one 3 IN (0.9 mm) Glo Stix section for improved tip visibility

Marketing Text 6

Optional Whisk Nose Tip is available for fishing over obstacles, and can be used to guide extended Glo Stix sideways above ceilings by rotating

Marketing Text 7

Can also be used to fish longer lengths by providing a tip that can be snagged from the opposite direction with another extended Fish or Glo Stix with a hook nose tip

PRODUCT SPECIFICATION –

Product Specification 1

Sub Brand : Fish Stix

Product Specification 2

Size : 1/4"x24' (6.4 mm x 7.3m)

Product Specification 3

Tensile Strength : 200.000 LB (0.900 KN) Maximum Pulling Strength

Product Specification 4

Color : Green

Product Specification 5

Diameter : 1/4 IN (6.400 MM)

Product Specification 6

Includes : Bullet And "J" Hook Nose Tips

Product Specification 7

Accessory : 10497 Hook Nose Tip, 10498 Bullet Nose Tip, 11426 Whisk Nose Tip

Product Specification 8

Replacement Part : 11583G 1/4 IN X 4 FT Fish Stix Section, 11584 1/4 IN X 6 FT Fish Stix Section, 12920 3/16 IN X 20 IN Glo Stix Section, 11585 3/16 IN x 3 FT Glo Stix Section, 11427 3/16 IN x 5 FT Glo Stix Section, 12922G 5/32 IN X 4 FT Glo Stix Section, 89803 5/32 IN X 6 FT

Product Specification 9

Minimum Bend Radius : 6-1/2 IN (165.000 MM)

Product Specification 10

Section Length : (3) 6.000 FT (1.800 M), (1) 3.000 FT (0.900 M) And (1) 3.000 FT (0.900 M) Glo Stix Section

Product Specification 11

Sections : 5