

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Strong, lightweight nylon. 595 - center feed for fast payout without tangling, use with Mighty Mouser blow gun. Mildew-resistant, can be pulled into the run with the wire to provide a means to add wires later. 604, 605, 606 and 607 - Specially wound to payout fast from outside without tangles

PRODUCT NAME –

Page Title

Nylon Conduit Fishline

PRODUCT OVERVIEW –

Marketing Text 1

Strong, lightweight nylon

Marketing Text 2

595 - center feed for fast payout without tangling, use with Mighty Mouser blow gun

Marketing Text 3

Mildew-resistant, can be pulled into the run with the wire to provide a means to add wires later

Marketing Text 4

604, 605, 606 and 607 - Specially wound to payout fast from outside without tangles

PRODUCT SPECIFICATION –

Product Specification 1

Tensile Strength : 85.000 LB (378.000 N) Breaking Strength

Product Specification 2

Material : Nylon