

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Improved cutting edge provides 30% longer life span. Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood. Unique patented design cutting angle - smoother starts, reduced cutting loads

PRODUCT NAME –

Page Title

1" Nail Eater[®] Bit

PRODUCT OVERVIEW –

Marketing Text 1

Improved cutting edge provides 30% longer life span

Marketing Text 2

Patented new design for improved cutting and cleaner holes

Marketing Text 3

Self-feeding screw point draws bit through wood

Marketing Text 4

Unique patented design cutting angle - smoother starts, reduced cutting loads

Marketing Text 5

Made of super tough, heat-treated steel

Marketing Text 6

Cuts through nails and provides longer life

Marketing Text 7

Shorty bits - for working in tight places, yet still can go through three abutting 2 x 4's

Marketing Text 8

See Bit Extensions if more length is required

Marketing Text 9

P.O.P packaged

PRODUCT SPECIFICATION –

Product Specification 1

Bit Diameter : 1.000 IN

Product Specification 2

D Chain : 4

Product Specification 3

Electric Drill Required : 61 PTS - 5/8 Through 61 PTS -1, Minimum 3/8 Drill, All BigShank, 1/2 Drill IN

Product Specification 4

Material : Heat Treated Steel

Product Specification 5

Material Master Number : 50366432

Product Specification 6

Overall Length : 7-5/8 IN

Product Specification 7

Shank Diameter : 7/16 IN

Product Specification 8

Shank Type : Hexagonal

Product Specification 9

Sub Brand : Nail Eater®

Product Specification 10

Twist Length : 5.000 IN

Product Specification 11

Type : Extreme Shorty

Product Specification 12

Weight : 0.700 LB (318.000 GM)

