

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Improved cutting edge provides 30% longer life span. Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood. Unique patented design cutting angle - smoother starts, reduced cutting loads

**PRODUCT NAME –**

---

**Page Title**

3/4" Nail Eater<sup>®</sup> Bit (66PT)

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Improved cutting edge provides 30% longer life span

**Marketing Text 2**

Patented new design for improved cutting and cleaner holes

**Marketing Text 3**

Self-feeding screw point draws bit through wood

**Marketing Text 4**

Unique patented design cutting angle - smoother starts, reduced cutting loads

### **Marketing Text 5**

Made of super tough, heat-treated steel

### **Marketing Text 6**

Cuts through nails and provides longer life

### **Marketing Text 7**

Shorty bits for working in tight places, yet still can go through three abutting 2 x4s

### **Marketing Text 8**

See Bit Extensions if more length is required

### **Marketing Text 9**

P.O.P packaged

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Bit Diameter : 3/4 IN

### **Product Specification 2**

D Chain : 4

### **Product Specification 3**

Material : Heat Treated Steel

### **Product Specification 4**

Overall Length : 18.000 IN

### **Product Specification 5**

Shank Diameter : 7/16 IN

### **Product Specification 6**

Shank Type : Hexagonal

### **Product Specification 7**

Sub Brand : Nail Eater

### **Product Specification 8**

Twist Length : 15.000 IN

### **Product Specification 9**

Type : Extreme

### **Product Specification 10**

Weight : 1.200 LB (545.000 GM)