

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Improved cutting edge provides 30% longer life span. Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood. Unique patented design cutting angle - smoother starts, reduced cutting loads

PRODUCT NAME –

Page Title

7/8" Nail Eater[®] Bit Bulk

PRODUCT OVERVIEW –

Marketing Text 1

Improved cutting edge provides 30% longer life span

Marketing Text 2

Patented new design for improved cutting and cleaner holes

Marketing Text 3

Self-feeding screw point draws bit through wood

Marketing Text 4

Unique patented design cutting angle - smoother starts, reduced cutting loads

Marketing Text 5

Made of super tough, heat-treated steel

Marketing Text 6

Cuts through nails and provides longer life

Marketing Text 7

Shorty bits for working in tight places, yet still can go through three abutting 2 x4s

Marketing Text 8

See Bit Extensions if more length is required

Marketing Text 9

P.O.P packaged

PRODUCT SPECIFICATION –

Product Specification 1

Bit Diameter : 7/8 IN

Product Specification 2

Material : Heat Treated Steel

Product Specification 3

Overall Length : 18.000 IN

Product Specification 4

Shank Diameter : 7/16 IN

Product Specification 5

Shank Type : Hexagonal

Product Specification 6

Sub Brand : Nail Eater®

Product Specification 7

Twist Length : 15.000 IN

Product Specification 8

Type : Extreme

Product Specification 9

Weight : 1.500 LB (681.000 GM)