

## **2024 Specification Sheet - English**

---



### **LONG DESCRIPTION –**

---

#### **Long Description Marketing Copy**

Caster bolt pattern 2-7/8 IN x 3-1/4 IN. Polyolefin-injected molded hard casters: stain-resistant, chemical-resistant, and non-marking

### **PRODUCT NAME –**

---

#### **Page Title**

2 Rigid, 2 Swivel

### **PRODUCT OVERVIEW –**

---

#### **Marketing Text 1**

Caster bolt pattern 2-7/8 IN x 3-1/4 IN

#### **Marketing Text 2**

Polyolefin-injected molded hard casters: stain-resistant, chemical-resistant, and non-marking

### **PRODUCT SPECIFICATION –**

---

#### **Product Specification 1**

Core Color : Black

#### **Product Specification 2**

Wheel Diameter : 4.000 IN (102.000 MM) 4 inches

**Product Specification 3**

Included : (2) Rigid, (2) Swivel, (16) 3/8-16 x 1 inches self-threading mounting screws (Cat# 06291)

**Product Specification 4**

Wheel Width : 2 inches

**Product Specification 5**

Wheel Material : Polyolefin

**Product Specification 6**

Capacity per Wheel : 400 pounds

**Product Specification 7**

Type : 2 Rigid, 2 Swivel Caster Set