

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Cuts through steel, tin, aluminum, fiberglass, wood and plastic. Deep 1-5/8 In cut to go through wood studs. Extra-tough bi-metal blade made of highest grade tool steel. Steam oxide finish for cooler running saw

PRODUCT NAME –

Page Title

2" Variable Pitch Hole Saw

PRODUCT OVERVIEW –

Marketing Text 1

Cuts through steel, tin, aluminum, fiberglass, wood and plastic

Marketing Text 2

Deep 1-5/8 In cut to go through wood studs

Marketing Text 3

Extra-tough bi-metal blade made of highest grade tool steel

Marketing Text 4

Steam oxide finish for cooler running saw

Marketing Text 5

Extra-thick backplate minimizes vibration

PRODUCT SPECIFICATION –

Product Specification 1

Application : Bi-Metal Hole Saw with 1-5/8 In cutting depth allowing cutting on 2x4 studs. Extra-thick backplate minimizes vibration for smoother, easier cutting.

Product Specification 2

Arbor Size : 7/16 In shank size.

Product Specification 3

Type : Bi-Metal Hole Saw

Product Specification 4

Cutting Size : 2 In