

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light. Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight. Strong, stable square hook design. 1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage

**PRODUCT NAME –**

---

**Page Title**

Iron Hand Bender Head for 3/4" EMT, 1/2" Rigid/IMC

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light

**Marketing Text 2**

Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight

**Marketing Text 3**

Strong, stable square hook design

#### **Marketing Text 4**

1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage

#### **Marketing Text 5**

1/2", 3/4" & 1" bender heads all have enlarged foot pedals and increased toe room to ensure greater control, stability and leverage

#### **Marketing Text 6**

All the bender handles area consistent diameter, offering a bigger grip area, while still straight up and down for fast 30 degree bends

#### **Marketing Text 7**

Lifetime Limited Warranty

### **PRODUCT SPECIFICATION –**

---

#### **Product Specification 1**

Centerline Bend Radius : 5-1/8" (130.200 MM)

#### **Product Specification 2**

Conduit Type : EMT, IMC, Rigid

#### **Product Specification 3**

Construction : Iron

#### **Product Specification 4**

Marking : 10, 22-1/2, 30, 45, 60 Degree

#### **Product Specification 5**

Pedal Type : Foot

#### **Product Specification 6**

Sub Brand : SITE-RITE

#### **Product Specification 7**

Type : Hand

#### **Product Specification 8**

Weight : 4.300 LB (2.000 KG)