

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light. Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight. Strong, stable square hook design 1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage. 1/2", 3/4" & 1" bender heads all have enlarged foot pedals and increased toe room to ensure greater control, stability and leverage

**PRODUCT NAME –**

---

**Page Title**

Bender,Hand-1" w/ Handle

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light

**Marketing Text 2**

Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight

### **Marketing Text 3**

Strong, stable square hook design 1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage

### **Marketing Text 4**

1/2", 3/4" & 1" bender heads all have enlarged foot pedals and increased toe room to ensure greater control, stability and leverage

### **Marketing Text 5**

All the bender handles area consistent diameter, offering a bigger grip area, while still straight up and down for fast 30-degree bends

### **Marketing Text 6**

Lifetime Limited Warranty

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Sub Brand Name Name : SITE-RITE

### **Product Specification 2**

Construction : Aluminum

### **Product Specification 3**

Centerline Bend Radius : 6-1/2" (165.100 MM)

### **Product Specification 4**

Conduit Size : 1" EMT3/4" Rigid/IMC

### **Product Specification 5**

Includes : Handle

### **Product Specification 6**

Type : Hand Bender

### **Product Specification 7**

Conduit Type : EMT, IMC, Rigid

### **Product Specification 8**

Marking : 10, 22-1/2, 30, 45, 60 Degree

### **Product Specification 9**

Pedal Type : Foot

### **Product Specification 10**

Application : Conduit Bending