

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light. Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight. Strong, stable square hook design. 1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage

PRODUCT NAME –

Page Title

Iron Hand Bender Head for 1-1/4" EMT, 1" Rigid/IMC

PRODUCT OVERVIEW –

Marketing Text 1

Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light

Marketing Text 2

Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight

Marketing Text 3

Strong, stable square hook design

Marketing Text 4

1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage

Marketing Text 5

1/2", 3/4" & 1" bender heads all have enlarged foot pedals and increased toe room to ensure greater control, stability and leverage

Marketing Text 6

All the bender handles area consistent diameter, offering a bigger grip area, while still straight up and down for fast 30 degree bends

Marketing Text 7

Lifetime Limited Warranty

PRODUCT SPECIFICATION –

Product Specification 1

Centerline Bend Radius : 9-5/8" (244.500 MM)

Product Specification 2

Conduit Type : EMT, IMC, Rigid

Product Specification 3

Construction : Iron

Product Specification 4

Marking : 10, 22-1/2, 30, 45, 60 Degree

Product Specification 5

Pedal Type : Foot

Product Specification 6

Sub Brand : SITE-RITE

Product Specification 7

Type : Hand

Product Specification 8

Weight : 16.200 LB (7.300 KG)