

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Measures incandescent, fluorescent, metal halide, high-pressure sodium and halogen lamp output. Color and cosine-corrected for enhanced accuracy. Measures up to 50,000 lux. Peak and data hold means no lost measurements

PRODUCT NAME –

Page Title

Digital Light Meter

PRODUCT OVERVIEW –

Marketing Text 1

Measures incandescent, fluorescent, metal halide, high-pressure sodium and halogen lamp output

Marketing Text 2

Color and cosine-corrected for enhanced accuracy

Marketing Text 3

Measures up to 50,000 lux

Marketing Text 4

Peak and data hold means no lost measurements

Marketing Text 5

Accessories included: (1) 9V battery and carrying case

Marketing Text 6

Lifetime Limited Warranty

PRODUCT SPECIFICATION –

Product Specification 1

Accuracy Incandescent Light Source : $\pm 4\%$

Product Specification 2

Accuracy Other Light Sources : $\pm 7\%$

Product Specification 3

Application : For Measures Incandescent, Fluorescent, Metal halide, High-Pressure Sodium And Halogen Lamp Output

Product Specification 4

Foot Candles : 0.01 - 5000 FC (20/200/2000/5000)

Product Specification 5

Includes : (1) 9V Battery And Carrying Case

Product Specification 6

LUX : 0.1 - 50000 LUX (200/2000/20000/50000)

Product Specification 7

Replacement Part : 06200 Carrying Case, 06061 Sensor, 06083 Sensor Case

Product Specification 8

Sampling Rate : 2.5 Times Per Second

Product Specification 9

Temperature Range : 0 - 40°C (32 - 104°F)

Product Specification 10

Type : Digital