

## **2024 Specification Sheet - English**

---



### **LONG DESCRIPTION –**

---

#### **Long Description Marketing Copy**

Deburs ID and OD of 1/2 IN, 3/4 IN and 1 IN thin wall conduit. Handle marked for easy identification. Hardened blade for longer life. Hooded, flat tip driver used to fasten EMT fittings

### **PRODUCT NAME –**

---

#### **Page Title**

Conduit Reaming Screwdriver

### **PRODUCT OVERVIEW –**

---

#### **Marketing Text 1**

Deburs ID and OD of 1/2 IN, 3/4 IN and 1 IN thin wall conduit

#### **Marketing Text 2**

Handle marked for easy identification

#### **Marketing Text 3**

Hardened blade for longer life

#### **Marketing Text 4**

Hooded, flat tip driver used to fasten EMT fittings

#### **Marketing Text 5**

Soft, cushioned grip for extra comfort and torque

### **Marketing Text 6**

Replaceable blade

### **Marketing Text 7**

Lifetime limited warranty

### **Marketing Text 8**

Note: This is not an insulated tool

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Capacity : 1/2 IN, 3/4 IN And 1.000 IN

### **Product Specification 2**

Handle Type : Soft, Cushioned Grip

### **Product Specification 3**

Overall Length : 7-7/16 IN (18.900 CM)

### **Product Specification 4**

Tip Type : Hooded, Flat

### **Product Specification 5**

Type : Conduit Reaming

### **Product Specification 6**

Weight : 0.490 LB (0.220 KG)