

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

AC amperage, AC/DC voltage measurement. True RMS for the most accurate measurement where harmonics are present. Quick, easy operation. Auto power off for longer battery life

PRODUCT NAME –

Page Title

AC True RMS Clamp Meter, 600V, 600A

PRODUCT OVERVIEW –

Marketing Text 1

AC amperage, AC/DC voltage measurement

Marketing Text 2

True RMS for the most accurate measurement where harmonics are present

Marketing Text 3

Quick, easy operation

Marketing Text 4

Auto power off for longer battery life

Marketing Text 5

Resistance measurement

Marketing Text 6

Audible continuity and diode tests

Marketing Text 7

Frequency measurement

Marketing Text 8

Data hold to capture measurement

Marketing Text 9

4000 count LCD

Marketing Text 10

Accessories included: Test leads, 3V Standard button battery (IEC-CR 2032; ANSI-NEDA 54004LC)

Marketing Text 11

Lifetime Limited Warranty

PRODUCT SPECIFICATION –

Product Specification 1

Amperage Measurement : 40, 400, 600 A AC

Product Specification 2

Display : LCD, 4000 Count

Product Specification 3

Includes : 3 V Standard Button Battery, Test Leads

Product Specification 4

Jaw Opening : 1.020 IN

Product Specification 5

Measurement Category : CAT III, 600 V Per UL 61010-1

Product Specification 6

Replacement Part : TSG-3 Sure-Grip Test Leads, TC-5 Carrying Case

Product Specification 7

Resistance Measurement : 400Ω

Product Specification 8

4, 40, 400kΩ

Product Specification 9

4, 40MΩ

Product Specification 10

Standard : CAT III, C/US UL Listed, CE

Product Specification 11

Type : AC, TRMS

Product Specification 12

Voltage Measurement : 4, 40, 400, 600 V AC

Product Specification 13

4, 40, 400, 600 V DC

Product Specification 14

400 mV