

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Measure Grounding Circuit Performance Without Disrupting Service. Reads ground resistance down to 0.10 Ω . Fully auto-ranging with data hold to capture readings. Accessories included: Molded carrying case, 9V Alkaline Battery and calibration verification loop

PRODUCT NAME –

Page Title

Ground Rod Tester

PRODUCT OVERVIEW –

Marketing Text 1

Measure Grounding Circuit Performance Without Disrupting Service

Marketing Text 2

Reads ground resistance down to 0.10 Ω

Marketing Text 3

Fully auto-ranging with data hold to capture readings

Marketing Text 4

Accessories included: Molded carrying case, 9V Alkaline Battery and calibration verification loop

Marketing Text 5

Impedance function capable of testing 4 separate frequencies (50Hz, 60Hz, 128Hz, & 2083Hz)

Marketing Text 6

Widest operating temperature range (- 4 to 131°F) in the industry

PRODUCT SPECIFICATION –

Product Specification 1

Display : 1.) OLED; Large, Bright2.) 3-3/4--digit, 4000 counts

Product Specification 2

Frequency : (4); 50, 60, 128, 2033Hz

Product Specification 3

Ground Resistance Measurement : .01 to 1500 ohms

Product Specification 4

Includes : Calibration Loop

Product Specification 5

Jaw Opening : 1.4

Product Specification 6

Measurement Category : Cat IV: 600V

Product Specification 7

Operation Type : Hand Held

Product Specification 8

Replacement Part : Calibration Loop

Product Specification 9

Resistance Measurement : .1 to 1500 ohms

Product Specification 10

Standard : CE, ETL