

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Oil-tempered spring steel for excellent fishing performance. Dirt-free tape finish keeps hands cleaner during use. Advanced comfort handle grip reduces fatigue. Superior rapid tape pay-out and rewind

PRODUCT NAME –

Page Title

100' Steel Fish Tape

PRODUCT OVERVIEW –

Marketing Text 1

Oil-tempered spring steel for excellent fishing performance

Marketing Text 2

Dirt-free tape finish keeps hands cleaner during use

Marketing Text 3

Advanced comfort handle grip reduces fatigue

Marketing Text 4

Superior rapid tape pay-out and rewind

Marketing Text 5

Smaller Fish Eye with offset bend for improved fishing ability

Marketing Text 6

Improved low profile tip for easy fishing through all sizes of conduit

Marketing Text 7

Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly

Marketing Text 8

Rugged case design improves drop impact capability

Marketing Text 9

Flared case with Grip Ridges for no slip handling

Marketing Text 10

Available in 50 FT (15

Marketing Text 11

2 m), 65 FT (19

Marketing Text 12

8 m), 125 FT (38

Marketing Text 13

1 m) and 240 FT (73

Marketing Text 14

2 m) lengths

Marketing Text 15

1/8 IN, 1/4 IN and flat steel profiles to accommodate different fishing situations

PRODUCT SPECIFICATION –

Product Specification 1

Sub Brand Name Name : MagnumPRO

Product Specification 2

Tensile Strength : 400.000 LB (1.700 KN) Maximum Design Strength

Product Specification 3

Material : Steel

Product Specification 4

Accessory : R438B Swivel Ball Head for use on 1/8 IN Steel Fish Tapes, R438-BM Ball Tip Male Half, 439-1 12 IN (305 MM) Flexible Fish Tape Leader, 439-2 12 IN (305 MM) SPEED FLEX Leader (solder joints)

Product Specification 5

Application : For Excellent Fishing Performance

Product Specification 6

Replacement Part : RS438W-100 Replacement Steel Tape - 100 FT X 1/4 IN (NO CASE), 10051G 8-1/2 IN Case/Handle Replacement Kit, 10052 12 IN Case/Handle Replacement Kit