

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Two die positions permit the KP1022 to crimp both insulated and uninsulated terminals and splices. Forged steel and hardened design provides long life. Smooth pivot action allowstool to easily be used with one hand. Double-cushioned handle grips on the KP1022 are easy on the hands

PRODUCT NAME –

Page Title

Terminal Crimping Tool with Molded Grip

PRODUCT OVERVIEW –

Marketing Text 1

Two die positions permit the KP1022 to crimp both insulated and uninsulated terminals and splices

Marketing Text 2

Forged steel and hardened design provides long life

Marketing Text 3

Smooth pivot action allowstool to easily be used with one hand

Marketing Text 4

Double-cushioned handle grips on the KP1022 are easy on the hands

Marketing Text 5

Precision machined and hardened cutter blades make wire cutting easy

PRODUCT SPECIFICATION –

Product Specification 1

Crimping Capacity : 22-10 AWG Insulated And Uninsulated Terminals And Splices

Product Specification 2

Handle Type : Double Cushioned And Molded Grip

Product Specification 3

Material : Forged Steel

Product Specification 4

Overall Length : 9-1/2 IN (241.000 MM)

Product Specification 5

Type : Terminal

Product Specification 6

Weight : 1.050 LB (0.480 KG)