

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Forged steel and hardened design provides long life. Smooth pivot action allows tool to easily be used with one hand. Standard handle grips on the KP1022D make it easy to slip in/out of tool pouches. Precision machined and hardened cutter blades make wire cutting easy

PRODUCT NAME –

Page Title

Terminal Crimping Tool with Dipped Grip

PRODUCT OVERVIEW –

Marketing Text 1

Forged steel and hardened design provides long life

Marketing Text 2

Smooth pivot action allows tool to easily be used with one hand

Marketing Text 3

Standard handle grips on the KP1022D make it easy to slip in/out of tool pouches

Marketing Text 4

Precision machined and hardened cutter blades make wire cutting easy

PRODUCT SPECIFICATION –

Product Specification 1

Crimping Capacity : 22-10 AWG Insulated And Uninsulated Terminals And Splices

Product Specification 2

Handle Type : Standard And Dipped Grip

Product Specification 3

Material : Forged Steel

Product Specification 4

Overall Length : 9-1/2 IN (241.000 MM)

Product Specification 5

Type : Terminal

Product Specification 6

Weight : 1.050 LB (0.480 KG)