

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Auto-Select Mode for hassle-free use. Low impedance eliminates stray or "ghost" voltage readings. AC/DC voltage measurement. Hassle-Free, automatic measurement of voltage and resistance

PRODUCT NAME –

Page Title

Pocket Multimeter, 450V

PRODUCT OVERVIEW –

Marketing Text 1

Auto-Select Mode for hassle-free use

Marketing Text 2

Low impedance eliminates stray or "ghost" voltage readings

Marketing Text 3

AC/DC voltage measurement

Marketing Text 4

Hassle-Free, automatic measurement of voltage and resistance

Marketing Text 5

Autoranging for quick, convenient measurements

Marketing Text 6

Non-contact voltage detection for identifying live lines without contacting conductors

Marketing Text 7

Intelligent Auto-Off for longer battery life

Marketing Text 8

Low battery indicator

Marketing Text 9

Resistance measurement

Marketing Text 10

Audible continuity test

Marketing Text 11

Frequency measurement in voltage mode

Marketing Text 12

Capacitance measurement

Marketing Text 13

6000-Count LCD for high resolution

Marketing Text 14

Accessories Included: (1) 3 V Battery (CR2032), Carrying Case

Marketing Text 15

Lifetime Limited Warranty

PRODUCT SPECIFICATION –

Product Specification 1

Battery : (1) 3 V

Product Specification 2

Capacitance : 100, 1000 nF; 10, 100 μF

Product Specification 3

Display : 6000-Count LCD For High Resolution

Product Specification 4

Includes : (1) 3 V Battery (CR2032), Carrying Case

Product Specification 5

Measurement Category : CAT II, 450 V, CAT III, 300 V

Product Specification 6

Resistance Measurement : 600 Ω , 6, 60, 600 k Ω , 6 M Ω

Product Specification 7

Standard : CAT III, CAT II, C/UL US Listed, CE Listed

Product Specification 8

Type : Pocket

Product Specification 9

Voltage Measurement : 6, 60, 450 V