

2024 Specification Sheet - English



LONG DESCRIPTION –

Long Description Marketing Copy

Oil-tempered spring steel for excellent fishing performance. Dirt-free tape finish keeps hands cleaner during use. Advanced comfort handle grip reduces fatigue. Superior rapid tape pay-out and rewind

PRODUCT NAME –

Page Title

1/4"X200' Steel Fish Tape (No Case)

PRODUCT OVERVIEW –

Marketing Text 1

Oil-tempered spring steel for excellent fishing performance

Marketing Text 2

Dirt-free tape finish keeps hands cleaner during use

Marketing Text 3

Advanced comfort handle grip reduces fatigue

Marketing Text 4

Superior rapid tape pay-out and rewind

Marketing Text 5

Smaller Fish Eye with offset bend for improved fishing ability

Marketing Text 6

Improved low profile tip for easy fishing through all sizes of conduit

Marketing Text 7

Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly

Marketing Text 8

Rugged case design improves drop impact capability

Marketing Text 9

Flared case with Grip Ridges for no slip handling

Marketing Text 10

Available in 50 FT (15.2 m), 65 FT (19.8 m), 125 FT (38.1 m) and 240 FT (73.2 m) lengths

Marketing Text 11

1/8 IN, 1/4 IN and flat steel profiles to accommodate different fishing situations

PRODUCT SPECIFICATION –

Product Specification 1

Accessory : R438B Swivel Ball Head for use on 1/8 IN Steel Fish Tapes, R438-BM Ball Tip Male Half, 439-1 12 IN (305 MM) Flexible Fish Tape Leader, 439-2 12 IN (305 MM) SPEED FLEX Leader (solder joints)

Product Specification 2

Application : For Excellent Fishing Performance

Product Specification 3

Length : 200.000 FT (61.000 M)

Product Specification 4

Material : Steel

Product Specification 5

Replacement Part : 10051G 8-1/2 IN Case/Handle Replacement Kit, 10052 12 IN Case/Handle Replacement Kit

Product Specification 6

Sub Brand : MagnumPRO

Product Specification 7

Tensile Strength : 400.000 LB (1.700 KN) Maximum Design Strength

Product Specification 8

Weight : 10.900 LB (4.900 KG)

Product Specification 9

Width : 1/4 IN (6.400 MM)