

# Pneumatic muffler AMTE-M-LH-G18

Part number: 1205860

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Pack size	20
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	1735 l/min
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	76 dB(A)
Ambient temperature	-40 °C ... 80 °C
Product weight	7.5 g
Pneumatic connection	G1/8
Cushioning insert material	Bronze
Material of screwed plug	Brass
Note on materials	RoHS-compliant