

Pneumatic muffler AMTE-M-LH-N18

Part number: 1206989

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Pack size	20
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	1615 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Noise level	77 dB(A)
Ambient temperature	-40 °C ... 80 °C
Product weight	9 g
Pneumatic connection	1/8 NPT
Cushioning insert material	Bronze
Material of screwed plug	Brass
Note on materials	RoHS-compliant