


Blanking plug QSC-10H

Part number: 153270

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Mounting position | Any |
| Design | Blanking plug |
| Pack size | 10 |
| Operating pressure for entire temperature range | -0.095 MPa ... 0.6 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 6 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 87 psi |
| Temperature-dependent operating pressure | -0.095 MPa ... 1.4 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 14 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 203 psi |
| Information on operating pressure | Water: max. 0.6 MPa at max. 50 °C |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Statically installed element, no meaningful evaluation possible according to ISO 14644-1 |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 2 g |
| Pneumatic connection 1 | Push-in sleeve Ø 10 mm |
| Note on materials | RoHS-compliant |
| Housing material | PBT |