

# Pneumatic muffler

## U-1/8

Part number: 2307



 [General operating condition](#)

### Data sheet

| Feature                                  | Value                                         |
|------------------------------------------|-----------------------------------------------|
| Mounting position                        | Any                                           |
| Symbol                                   | 00991473                                      |
| Operating pressure                       | 0 MPa ... 1 MPa                               |
| Operating pressure                       | 0 bar ... 10 bar                              |
| Flow rate with respect to atmosphere     | 2000 l/min                                    |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible       |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L                             |
| Noise level                              | 74 dB(A)                                      |
| Ambient temperature                      | -10 °C ... 70 °C                              |
| Product weight                           | 2.3 g                                         |
| Pneumatic connection                     | G1/8                                          |
| Cushioning insert material               | PE                                            |
| Note on materials                        | RoHS-compliant                                |