

# Push-in L-fitting QBL-1/4-1/4-U

Part number: 533295

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Standard
Nominal width	4.496 mm
Type of seal on screwed plug	Coating
Mounting position	Any
Design	L-shape
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	0.95 bar ... 10 bar
Operating pressure for entire temperature range	13.775 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	12 Nm
Product weight	19.703 g
Type of mounting	External hexagon 9/16
Pneumatic connection 1	external thread 1/4 NPT
Pneumatic connection 2	for pneumatic tubing outer diameter 1/4"
Ambient temperature Fahrenheit	32 °F ... 140 °F
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated PBT
Material of threaded seal	PTFE
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel