

Adapter
AD-1NPT-G1-I
Part number: 546547



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	24.2 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	35 Nm
Max. tightening torque, pneumatic connection 2	90 Nm
Product weight	218.86 g
Pneumatic connection 1	External thread 1 NPT
Pneumatic connection 2	Female thread G1
Note on materials	RoHS-compliant
Seals material	PVC
Housing material	Steel, galvanized