

# Blanking plug QBC-1/2H-U

Part number: 564789

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	Standard
Mounting position	Any
Design	Blanking plug
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	0.95 bar ... 10 bar
Operating pressure for entire temperature range	13.775 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C ... 60 °C
Product weight	3.005 g
Pneumatic connection 1	Push-in sleeve Ø 1/2"
Ambient temperature Fahrenheit	32 °F ... 140 °F
Note on materials	RoHS-compliant