

Adapter
AD-G1/4-1/4NPT-I
Part number: 9396



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	7.95 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	11 Nm
Max. tightening torque, pneumatic connection 2	12 Nm
Nominal tightening torque	9.05 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	24.22 g
Pneumatic connection 1	External thread G1/4
Pneumatic connection 2	Internal thread 1/4 NPT
Note on materials	RoHS-compliant
Seals material	PVC
Housing material	Steel, galvanized