

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Improved cutting edge provides 30% longer life span. Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood. Unique patented design cutting angle - smoother starts, reduced cutting loads. Made of super tough, heat-treated steel

PRODUCT NAME –

Page Title

1-1/8 X 7.62 Nail Eater[®] Bit

PRODUCT OVERVIEW –

Marketing Text 1

Improved cutting edge provides 30% longer life span

Marketing Text 2

Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood

Marketing Text 3

Unique patented design cutting angle - smoother starts, reduced cutting loads

Marketing Text 4

Made of super tough, heat-treated steel

Marketing Text 5

Cuts through nails and provides longer life

Marketing Text 6

Shorty bits - for working in tight places, yet still can go through three abutting 2 x 4s

Marketing Text 7

P.O.P packaged

PRODUCT SPECIFICATION –

Product Specification 1

Bit Diameter : 1-1/8 IN (28.600 MM)

Product Specification 2

Electric Drill Required : 61 PTS - 5/8 Through 61 PTS -1, Minimum 3/8 IN Drill, All Big Shank, 1/2 IN Drill

Product Specification 3

Material : Heat Treated Steel

Product Specification 4

Overall Length : 7-5/8 IN (193.700 MM)

Product Specification 5

Shank Diameter : 7/16 IN (11.100 MM)

Product Specification 6

Shank Type : Hexagonal

Product Specification 7

Sub Brand : Nail Eater®

Product Specification 8

Twist Length : 5.000 IN (127.000 MM)

Product Specification 9

Type : Extreme Shorty

Product Specification 10

Weight : 0.900 LB (409.000 GM)