

## 2024 Specification Sheet - English

---



### LONG DESCRIPTION –

---

#### **Long Description Marketing Copy**

Large, easy-to-read displays. Lifetime warranty. Feature packed. Replaceable fuses for easy field repair

### PRODUCT NAME –

---

#### **Page Title**

Manual Ranging Digital Multimeter, 600V (DM-25)

### PRODUCT OVERVIEW –

---

#### **Marketing Text 1**

Large, easy-to-read displays

#### **Marketing Text 2**

Lifetime warranty

#### **Marketing Text 3**

Feature packed

#### **Marketing Text 4**

Replaceable fuses for easy field repair

#### **Marketing Text 5**

Frequency, capacitance, duty cycle, temperature, battery test and analog bar graph are just some of the features available on these meters

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Battery : Yes

### **Product Specification 2**

Counts : 2000

### **Product Specification 3**

Diode Test : Yes

### **Product Specification 4**

Display : Digital

### **Product Specification 5**

Field Replaceable Fuses : No

### **Product Specification 6**

Resistance : 200, 2000  $\Omega$ ; 20, 200, 2000 k $\Omega$

### **Product Specification 7**

Standard : C/US ETL Listed, CATIII Approved

### **Product Specification 8**

Type : Manual Ranging

### **Product Specification 9**

Voltage Rating : 600