

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app. Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback. Designed primarily to cut distribution ACSR cable Powerful state of the art 18V lithium ion (Li-ion) battery LED light provides the operator with the battery charge and tool maintenance status In-line tool style is light weight and very easy to control One trigger controls all tool functions Cutting head rotates 350° Tool automatically retracts when the cutting cycle is complete Over molded tacky grip areas make gripping the tool easier and more comfortable LED work light illuminates dark work areas Uses bio-degradable oil Smart Chargers control the charging current, charging voltage and battery temperature to maximize battery life Available with 120V, 12V, or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger. Designed primarily to cut distribution ACSR cable Powerful state of the art 18V lithium ion (Li-ion) battery LED light provides the operator with the battery charge and tool maintenance status In-line tool style is light weight and very easy to control One trigger controls all tool functions Cutting head rotates 350° Tool automatically retracts when the cutting cycle is complete Overmolded tacky grip areas make gripping the tool easier and more comfortable LED work light illuminates dark work areas Uses bio-degradable oil Smart Chargers control the charging current, charging voltage and battery temperature to maximize battery life. Available with 120V, 12V, or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger

**PRODUCT NAME –**

---

Wire Cutter 25mm, Li-ion, Standard, Bare

## **PRODUCT OVERVIEW –**

---

### **Marketing Text 1**

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app. Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback. Designed primarily to cut distribution ACSR cable Powerful state of the art 18V lithium ion (Li-ion) battery LED light provides the operator with the battery charge and tool maintenance status In-line tool style is light weight and very easy to control One trigger controls all tool functions Cutting head rotates 350° Tool automatically retracts when the cutting cycle is complete Over molded tacky grip areas make gripping the tool easier and more comfortable LED work light illuminates dark work areas Uses bio-degradable oil Smart Chargers control the charging current, charging voltage and battery temperature to maximize battery life Available with 120V, 12V, or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger

### **Marketing Text 2**

Designed primarily to cut distribution ACSR cable Powerful state of the art 18V lithium ion (Li-ion) battery LED light provides the operator with the battery charge and tool maintenance status In-line tool style is light weight and very easy to control One trigger controls all tool functions Cutting head rotates 350° Tool automatically retracts when the cutting cycle is complete Overmolded tacky grip areas make gripping the tool easier and more comfortable LED work light illuminates dark work areas Uses bio-degradable oil Smart Chargers control the charging current, charging voltage and battery temperature to maximize battery life. Available with 120V, 12V, or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Sub Brand : Gator

### **Product Specification 2**

Type : Guillotine Style Cutter

### **Product Specification 3**

Application : ACSR, Guy Strand, Steel

### **Product Specification 4**

Cutting Edge : Hard Metal, Steel

### **Product Specification 5**

Cutting Range : Cutter Head Opening: 1.000 IN (25.000 MM)

### **Product Specification 6**

Cutting Range : ACSR: 636 KCMIL

### **Product Specification 7**

Cutting Range : Guy Strand (Not EHS): 5/8 IN (16.000 MM)

### **Product Specification 8**

Cutting Range : Ground Rod: 3/8 IN (9.000 MM)

**Product Specification 9**

Cutting Range : Rebar (SCH 60): 3/8 IN (9.000 MM)

**Product Specification 10**

Cutting Range : Wire Rope: 1/2 IN (13.000 MM)Cu

**Product Specification 11**

Jaw Size : .98 IN (25mm)

**Product Specification 12**

Overall Length : 15 IN (381mm)

**Product Specification 13**

Handle Type : In-line style with over molded rubber grip

**Product Specification 14**

Finish : Black